

SAFETY DATA SHEET

1. Identification

Product number 1000014373
Product identifier **CLEAN CHOICE APPLE AIR FRESHENER**
Company information FASTENAL
2001 THEURER BLVD
WINONA, MN 55987 United States
Emergency telephone US 1-866-836-8855
Emergency telephone outside US 1-952-852-4646
Version # 01
Recommended use AIR FRESHENER
Recommended restrictions None known.

2. Hazard(s) identification

Physical hazards Flammable aerosols Category 1
Health hazards Serious eye damage/eye irritation Category 2A
Specific target organ toxicity, single exposure Category 3 narcotic effects
OSHA defined hazards Not classified.

Label elements



Signal word Danger
Hazard statement Extremely flammable aerosol. Causes serious eye irritation. May cause drowsiness or dizziness.
Precautionary statement
Prevention Keep away from heat/sparks/open flames/hot surfaces. - No smoking. Do not spray on an open flame or other ignition source. Pressurized container: Do not pierce or burn, even after use. Avoid breathing gas. Wash thoroughly after handling. Use only outdoors or in a well-ventilated area. Wear eye protection/face protection.
Response If inhaled: Remove person to fresh air and keep comfortable for breathing. If in eyes: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. Call a poison center/doctor if you feel unwell. If eye irritation persists: Get medical advice/attention.
Storage Store in a well-ventilated place. Keep container tightly closed. Store locked up. Protect from sunlight. Do not expose to temperatures exceeding 50°C/122°F.
Disposal Dispose of contents/container in accordance with local/regional/national/international regulations.
Hazard(s) not otherwise classified (HNOC) None known.
Supplemental information None.

3. Composition/information on ingredients

Mixtures

Chemical name	Common name and synonyms	CAS number	%
Acetone		67-64-1	60 - 80
Butane		106-97-8	10 - 20
Propane		74-98-6	10 - 20
2-tert-butylcyclohexyl Acetate		88-41-5	0.1 - 1
Other components below reportable levels			1 - 2.5

*Designates that a specific chemical identity and/or percentage of composition has been withheld as a trade secret.

4. First-aid measures

Inhalation	Remove victim to fresh air and keep at rest in a position comfortable for breathing. Call a POISON CENTER or doctor/physician if you feel unwell.
Skin contact	Wash off with soap and water. Get medical attention if irritation develops and persists.
Eye contact	Immediately flush eyes with plenty of water for at least 15 minutes. Remove contact lenses, if present and easy to do. Continue rinsing. If eye irritation persists: Get medical advice/attention.
Ingestion	In the unlikely event of swallowing contact a physician or poison control center. Rinse mouth.
Most important symptoms/effects, acute and delayed	May cause drowsiness and dizziness. Headache. Nausea, vomiting. Severe eye irritation. Symptoms may include stinging, tearing, redness, swelling, and blurred vision.
Indication of immediate medical attention and special treatment needed	Provide general supportive measures and treat symptomatically. Keep victim under observation. Symptoms may be delayed.
General information	Ensure that medical personnel are aware of the material(s) involved, and take precautions to protect themselves.

5. Fire-fighting measures

Suitable extinguishing media	Alcohol resistant foam. Powder. Carbon dioxide (CO ₂).
Unsuitable extinguishing media	Do not use water jet as an extinguisher, as this will spread the fire.
Specific hazards arising from the chemical	Contents under pressure. Pressurized container may explode when exposed to heat or flame. During fire, gases hazardous to health may be formed.
Special protective equipment and precautions for firefighters	Firefighters must use standard protective equipment including flame retardant coat, helmet with face shield, gloves, rubber boots, and in enclosed spaces, SCBA.
Fire fighting equipment/instructions	Move containers from fire area if you can do so without risk. Containers should be cooled with water to prevent vapor pressure build up. For massive fire in cargo area, use unmanned hose holder or monitor nozzles, if possible. If not, withdraw and let fire burn out.
Specific methods	Use standard firefighting procedures and consider the hazards of other involved materials. Move containers from fire area if you can do so without risk. In the event of fire and/or explosion do not breathe fumes.
General fire hazards	Extremely flammable aerosol.

6. Accidental release measures

Personal precautions, protective equipment and emergency procedures	Keep unnecessary personnel away. Keep people away from and upwind of spill/leak. Wear appropriate protective equipment and clothing during clean-up. Avoid breathing gas. Do not touch damaged containers or spilled material unless wearing appropriate protective clothing. Ventilate closed spaces before entering them. Local authorities should be advised if significant spillages cannot be contained. For personal protection, see section 8 of the SDS.
Methods and materials for containment and cleaning up	Refer to attached safety data sheets and/or instructions for use. Stop leak if you can do so without risk. Move the cylinder to a safe and open area if the leak is irreparable. Isolate area until gas has dispersed. Eliminate all ignition sources (no smoking, flares, sparks, or flames in immediate area). Keep combustibles (wood, paper, oil, etc.) away from spilled material. Cover with plastic sheet to prevent spreading. Absorb in vermiculite, dry sand or earth and place into containers. Following product recovery, flush area with water. Small Spills: Wipe up with absorbent material (e.g. cloth, fleece). Clean surface thoroughly to remove residual contamination. For waste disposal, see section 13 of the SDS.
Environmental precautions	Avoid discharge into drains, water courses or onto the ground.

7. Handling and storage

Precautions for safe handling	Pressurized container: Do not pierce or burn, even after use. Do not use if spray button is missing or defective. Do not spray on a naked flame or any other incandescent material. Do not smoke while using or until sprayed surface is thoroughly dry. Do not cut, weld, solder, drill, grind, or expose containers to heat, flame, sparks, or other sources of ignition. All equipment used when handling the product must be grounded. Do not re-use empty containers. Avoid breathing gas. Avoid contact with eyes. Avoid prolonged exposure. Use only in well-ventilated areas. Wear appropriate personal protective equipment. Observe good industrial hygiene practices.
--------------------------------------	--

Conditions for safe storage, including any incompatibilities

Level 3 Aerosol.

Store locked up. Pressurized container. Protect from sunlight and do not expose to temperatures exceeding 50°C/122 °F. Do not puncture, incinerate or crush. Do not handle or store near an open flame, heat or other sources of ignition. This material can accumulate static charge which may cause spark and become an ignition source. Store away from incompatible materials (see Section 10 of the SDS).

8. Exposure controls/personal protection**Occupational exposure limits****US. OSHA Table Z-1 Limits for Air Contaminants (29 CFR 1910.1000)**

Components	Type	Value
Acetone (CAS 67-64-1)	PEL	2400 mg/m3 1000 ppm
Propane (CAS 74-98-6)	PEL	1800 mg/m3 1000 ppm

US. ACGIH Threshold Limit Values

Components	Type	Value
Acetone (CAS 67-64-1)	STEL	500 ppm
	TWA	250 ppm
Butane (CAS 106-97-8)	STEL	1000 ppm

US. NIOSH: Pocket Guide to Chemical Hazards

Components	Type	Value
Acetone (CAS 67-64-1)	TWA	590 mg/m3 250 ppm
Butane (CAS 106-97-8)	TWA	1900 mg/m3 800 ppm
Propane (CAS 74-98-6)	TWA	1800 mg/m3 1000 ppm

Biological limit values**ACGIH Biological Exposure Indices**

Components	Value	Determinant	Specimen	Sampling Time
Acetone (CAS 67-64-1)	25 mg/l	Acetone	Urine	*

* - For sampling details, please see the source document.

Appropriate engineering controls

Good general ventilation (typically 10 air changes per hour) should be used. Ventilation rates should be matched to conditions. If applicable, use process enclosures, local exhaust ventilation, or other engineering controls to maintain airborne levels below recommended exposure limits. If exposure limits have not been established, maintain airborne levels to an acceptable level. Provide eyewash station.

Individual protection measures, such as personal protective equipment

Eye/face protection Wear safety glasses with side shields (or goggles).

Skin protection

Hand protection Wear appropriate chemical resistant gloves. Suitable gloves can be recommended by the glove supplier.

Other Wear suitable protective clothing.

Respiratory protection If permissible levels are exceeded use NIOSH mechanical filter / organic vapor cartridge or an air-supplied respirator.

Thermal hazards Wear appropriate thermal protective clothing, when necessary.

General hygiene considerations

When using do not smoke. Always observe good personal hygiene measures, such as washing after handling the material and before eating, drinking, and/or smoking. Routinely wash work clothing and protective equipment to remove contaminants.

9. Physical and chemical properties**Appearance**

Physical state	Gas.
Form	Aerosol.

Color	Not available.
Odor	Not available.
Odor threshold	Not available.
pH	Not available.
Melting point/freezing point	Not available.
Initial boiling point and boiling range	132.89 °F (56.05 °C) estimated
Flash point	-156.0 °F (-104.4 °C) PROPELLANT estimated
Evaporation rate	Not available.
Flammability (solid, gas)	Not available.
Upper/lower flammability or explosive limits	
Flammability limit - lower (%)	2.4 % estimated
Flammability limit - upper (%)	11.8 % estimated
Explosive limit - lower (%)	Not available.
Explosive limit - upper (%)	Not available.
Vapor pressure	60 - 70 psig @70F estimated
Vapor density	Not available.
Relative density	Not available.
Solubility(ies)	
Solubility (water)	Not available.
Partition coefficient (n-octanol/water)	Not available.
Auto-ignition temperature	869 °F (465 °C) estimated
Decomposition temperature	Not available.
Viscosity	Not available.
Other information	
Density	0.73 g/cm3 estimated
Explosive properties	Not explosive.
Heat of combustion (NFPA 30B)	32.54 kJ/g estimated
Oxidizing properties	Not oxidizing.
Specific gravity	0.784 estimated
VOC (Weight %)	30.29 %

10. Stability and reactivity

Reactivity	The product is stable and non-reactive under normal conditions of use, storage and transport.
Chemical stability	Material is stable under normal conditions.
Possibility of hazardous reactions	Hazardous polymerization does not occur.
Conditions to avoid	Avoid temperatures exceeding the flash point. Contact with incompatible materials.
Incompatible materials	Strong oxidizing agents. Nitrates. Fluorine. Chlorine.
Hazardous decomposition products	No hazardous decomposition products are known.

11. Toxicological information

Information on likely routes of exposure

Inhalation	May cause drowsiness and dizziness. Headache. Nausea, vomiting. Prolonged inhalation may be harmful.
Skin contact	No adverse effects due to skin contact are expected.
Eye contact	Causes serious eye irritation.
Ingestion	Expected to be a low ingestion hazard.

Symptoms related to the physical, chemical and toxicological characteristics

May cause drowsiness and dizziness. Headache. Nausea, vomiting. Severe eye irritation. Symptoms may include stinging, tearing, redness, swelling, and blurred vision.

Information on toxicological effects

Acute toxicity

Narcotic effects.

Components

Species

Test Results

Acetone (CAS 67-64-1)

Acute

Dermal

LD50

Guinea pig

> 7426 mg/kg, 24 Hours

> 9.4 ml/kg, 24 Hours

Rabbit

> 7426 mg/kg, 24 Hours

> 9.4 ml/kg, 24 Hours

Inhalation

LC50

Rat

55700 ppm, 3 Hours

132 mg/l, 3 Hours

50.1 mg/l

Oral

LD50

Rat

5800 mg/kg

2.2 ml/kg

Butane (CAS 106-97-8)

Acute

Inhalation

LC50

Mouse

1237 mg/l, 120 Minutes

52 %, 120 Minutes

Rat

1355 mg/l

Propane (CAS 74-98-6)

Acute

Inhalation

LC50

Mouse

1237 mg/l, 120 Minutes

52 %, 120 Minutes

Rat

1355 mg/l

658 mg/l/4h

* Estimates for product may be based on additional component data not shown.

Skin corrosion/irritation

Prolonged skin contact may cause temporary irritation.

Serious eye damage/eye irritation

Causes serious eye irritation.

Respiratory or skin sensitization

Respiratory sensitization

Not a respiratory sensitizer.

Skin sensitization

This product is not expected to cause skin sensitization.

Germ cell mutagenicity

No data available to indicate product or any components present at greater than 0.1% are mutagenic or genotoxic.

Carcinogenicity

This product is not considered to be a carcinogen by IARC, ACGIH, NTP, or OSHA.

IARC Monographs. Overall Evaluation of Carcinogenicity

Not listed.

OSHA Specifically Regulated Substances (29 CFR 1910.1001-1050)

Not regulated.

US. National Toxicology Program (NTP) Report on Carcinogens

Not listed.

Reproductive toxicity

This product is not expected to cause reproductive or developmental effects.

Specific target organ toxicity - single exposure	May cause drowsiness and dizziness.
Specific target organ toxicity - repeated exposure	Not classified.
Aspiration hazard	Not likely, due to the form of the product.
Chronic effects	Prolonged inhalation may be harmful.

12. Ecological information

Ecotoxicity The product is not classified as environmentally hazardous. However, this does not exclude the possibility that large or frequent spills can have a harmful or damaging effect on the environment.

Components	Species	Test Results
Acetone (CAS 67-64-1)		
Aquatic		
Crustacea	EC50	Water flea (Daphnia magna) 21.6 - 23.9 mg/l, 48 hours
Fish	LC50	Rainbow trout, donaldson trout (Oncorhynchus mykiss) 4740 - 6330 mg/l, 96 hours

* Estimates for product may be based on additional component data not shown.

Persistence and degradability No data is available on the degradability of this product.

Bioaccumulative potential

Partition coefficient n-octanol / water (log Kow)

Acetone	-0.24
Butane	2.89
Propane	2.36

Mobility in soil No data available.

Other adverse effects No other adverse environmental effects (e.g. ozone depletion, photochemical ozone creation potential, endocrine disruption, global warming potential) are expected from this component.

13. Disposal considerations

Disposal instructions Collect and reclaim or dispose in sealed containers at licensed waste disposal site. Contents under pressure. Do not puncture, incinerate or crush. Dispose of contents/container in accordance with local/regional/national/international regulations.

Local disposal regulations Dispose in accordance with all applicable regulations.

Hazardous waste code The waste code should be assigned in discussion between the user, the producer and the waste disposal company.

Waste from residues / unused products Dispose of in accordance with local regulations. Empty containers or liners may retain some product residues. This material and its container must be disposed of in a safe manner (see: Disposal instructions).

Contaminated packaging Since emptied containers may retain product residue, follow label warnings even after container is emptied. Empty containers should be taken to an approved waste handling site for recycling or disposal. Do not re-use empty containers.

14. Transport information

DOT

UN number	UN1950
UN proper shipping name	Aerosols, flammable, (each not exceeding 1 L capacity)
Transport hazard class(es)	
Class	2.1
Subsidiary risk	-
Label(s)	2.1
Packing group	Not applicable.
Special precautions for user	Read safety instructions, SDS and emergency procedures before handling.
Special provisions	N82
Packaging exceptions	306
Packaging non bulk	None
Packaging bulk	None

This product meets the exception requirements of section 173.306 as a limited quantity and may be shipped as a limited quantity. Until 12/31/2020, the "Consumer Commodity - ORM-D" marking may still be used in place of the new limited quantity diamond mark for packages of UN 1950 Aerosols. Limited quantities require the limited quantity diamond mark on cartons after 12/31/20 and may be used now in place of the "Consumer Commodity ORM-D" marking.

IATA

UN number	UN1950
UN proper shipping name	Aerosols, flammable
Transport hazard class(es)	
Class	2.1
Subsidiary risk	-
Label(s)	2.1
Packing group	Not applicable.
Environmental hazards	No.
ERG Code	10L
Special precautions for user	Read safety instructions, SDS and emergency procedures before handling. Read safety instructions, SDS and emergency procedures before handling.
Other information	
Passenger and cargo aircraft	Allowed with restrictions.
Cargo aircraft only	Allowed with restrictions.
Packaging Exceptions	LTD QTY

IMDG

UN number	UN1950
UN proper shipping name	AEROSOLS
Transport hazard class(es)	
Class	2.1
Subsidiary risk	-
Label(s)	None
Packing group	Not applicable.
Environmental hazards	
Marine pollutant	No.
EmS	F-D, S-U
Special precautions for user	Read safety instructions, SDS and emergency procedures before handling. Read safety instructions, SDS and emergency procedures before handling.
Packaging Exceptions	LTD QTY

Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code Not applicable.

DOT



IATA; IMDG



15. Regulatory information

US federal regulations This product is a "Hazardous Chemical" as defined by the OSHA Hazard Communication Standard, 29 CFR 1910.1200.

TSCA Section 12(b) Export Notification (40 CFR 707, Subpt. D)

Not regulated.

CERCLA Hazardous Substance List (40 CFR 302.4)

Acetone (CAS 67-64-1) Listed.

SARA 304 Emergency release notification

Not regulated.

OSHA Specifically Regulated Substances (29 CFR 1910.1001-1050)

Not regulated.

Superfund Amendments and Reauthorization Act of 1986 (SARA)

Hazard categories
Immediate Hazard - Yes
Delayed Hazard - No
Fire Hazard - Yes
Pressure Hazard - Yes
Reactivity Hazard - No

SARA 302 Extremely hazardous substance

Not listed.

SARA 311/312 Hazardous chemical No

SARA 313 (TRI reporting)

Not regulated.

Other federal regulations

Clean Air Act (CAA) Section 112 Hazardous Air Pollutants (HAPs) List

Not regulated.

Clean Air Act (CAA) Section 112(r) Accidental Release Prevention (40 CFR 68.130)

Butane (CAS 106-97-8)

Propane (CAS 74-98-6)

Safe Drinking Water Act (SDWA) Not regulated.

Drug Enforcement Administration (DEA). List 2, Essential Chemicals (21 CFR 1310.02(b) and 1310.04(f)(2) and Chemical Code Number

Acetone (CAS 67-64-1) 6532

Drug Enforcement Administration (DEA). List 1 & 2 Exempt Chemical Mixtures (21 CFR 1310.12(c))

Acetone (CAS 67-64-1) 35 %WV

DEA Exempt Chemical Mixtures Code Number

Acetone (CAS 67-64-1) 6532

US state regulations

US. California Controlled Substances. CA Department of Justice (California Health and Safety Code Section 11100)

Not listed.

US. California. Candidate Chemicals List. Safer Consumer Products Regulations (Cal. Code Regs, tit. 22, 69502.3, subd. (a))

Acetone (CAS 67-64-1)

Butane (CAS 106-97-8)

US. Massachusetts RTK - Substance List

Acetone (CAS 67-64-1)

Butane (CAS 106-97-8)

Propane (CAS 74-98-6)

US. New Jersey Worker and Community Right-to-Know Act

Acetone (CAS 67-64-1)

Butane (CAS 106-97-8)

Propane (CAS 74-98-6)

US. Pennsylvania Worker and Community Right-to-Know Law

Acetone (CAS 67-64-1)

Butane (CAS 106-97-8)

Propane (CAS 74-98-6)

US. Rhode Island RTK

Acetone (CAS 67-64-1)

Butane (CAS 106-97-8)

Propane (CAS 74-98-6)

US. California Proposition 65

California Safe Drinking Water and Toxic Enforcement Act of 1986 (Proposition 65): This material is not known to contain any chemicals currently listed as carcinogens or reproductive toxins.

International Inventories

Country(s) or region	Inventory name	On inventory (yes/no)*
Australia	Australian Inventory of Chemical Substances (AICS)	No
Canada	Domestic Substances List (DSL)	Yes
Canada	Non-Domestic Substances List (NDSL)	No
China	Inventory of Existing Chemical Substances in China (IECSC)	No
Europe	European Inventory of Existing Commercial Chemical Substances (EINECS)	No
Europe	European List of Notified Chemical Substances (ELINCS)	No
Japan	Inventory of Existing and New Chemical Substances (ENCS)	No
Korea	Existing Chemicals List (ECL)	No
New Zealand	New Zealand Inventory	No
Philippines	Philippine Inventory of Chemicals and Chemical Substances (PICCS)	No
United States & Puerto Rico	Toxic Substances Control Act (TSCA) Inventory	Yes

*A "Yes" indicates that all components of this product comply with the inventory requirements administered by the governing country(s)

A "No" indicates that one or more components of the product are not listed or exempt from listing on the inventory administered by the governing country(s).

16. Other information, including date of preparation or last revision

Issue date	02-12-2019
Version #	01
Disclaimer	The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text.
Revision information	Product and Company Identification: Alternate Trade Names