



Revision Number: 003.3

Issue date: 10/05/2018

1. PRODUCT AND COMPANY IDENTIFICATION

Product name:	LOCTITE EA 9017 B known as LOCTITE FM POXY PAK 1FO PT B	IDH number:	1324014
Product type:	Epoxy Hardener	Item number:	1324007_1295955
Restriction of Use:	None identified	Region:	United States
Company address:	Contact information: Telephone: +1 (860) 571-5100 MEDICAL EMERGENCY Phone: Poison Control Center 1-877-671-4608 (toll free) or 1-303-592-1711 TRANSPORT EMERGENCY Phone: CHEMTREC 1-800-424-9300 (toll free) or 1-703-527-3887 Internet: www.henkelna.com		
Henkel Corporation One Henkel Way Rocky Hill, Connecticut 06067			

2. HAZARDS IDENTIFICATION

EMERGENCY OVERVIEW

DANGER: CAUSES SEVERE SKIN BURNS AND EYE DAMAGE.
 MAY CAUSE AN ALLERGIC SKIN REACTION.
 SUSPECTED OF CAUSING GENETIC DEFECTS.
 MAY CAUSE DAMAGE TO ORGANS THROUGH PROLONGED OR
 REPEATED EXPOSURE.

HAZARD CLASS	HAZARD CATEGORY
SKIN CORROSION	1B
SERIOUS EYE DAMAGE	1
SKIN SENSITIZATION	1
GERM CELL MUTAGENICITY	2
SPECIFIC TARGET ORGAN TOXICITY - REPEATED EXPOSURE	2

PICTOGRAM(S)



Precautionary Statements

Prevention:	Obtain special instructions before use. Do not handle until all safety precautions have been read and understood. Do not breathe vapors, mist, or spray. Wash affected area thoroughly after handling. Contaminated work clothing should not be allowed out of the workplace. Wear protective gloves, clothing, eye and face protection.
Response:	IF SWALLOWED: Rinse mouth. Do NOT induce vomiting. If on skin (or hair): Take off immediately all contaminated clothing. IF INHALED: Remove victim to fresh air and keep at rest in a position comfortable for breathing. Immediately call a POISON CENTER or physician. IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. IF exposed or concerned: Get medical attention. If skin irritation or rash occurs: Get medical attention. Wash contaminated clothing before reuse.
Storage:	Store locked up.
Disposal:	Dispose of contents and/or container according to Federal, State/Provincial and local governmental regulations.

Classification complies with OSHA Hazard Communication Standard (29 CFR 1910.1200) and is consistent with the provisions of the United Nations Globally Harmonized System of Classification and Labeling of Chemicals (GHS).

See Section 11 for additional toxicological information.

3. COMPOSITION / INFORMATION ON INGREDIENTS

Hazardous Component(s)	CAS Number	Percentage*
Poly[oxy(methyl-1,2-ethanediyl)], a-hydroxy-hydroxy-, ether with 2,2-bis(hydroxymethyl)-1,3-propanediol (4:1), 2-hydroxy-3-mercaptopy	72244-98-5	70 - 80
m-Phenylenebis(methylamine)	1477-55-0	10 - 20
2,4,6-Tris(dimethylaminomethyl)phenol	90-72-2	5 - 10
Phenol	108-95-2	1 - 5
3-(Trimethoxysilyl)propylamine	13822-56-5	0.1 - 1
Bis[(dimethylamino)methyl]phenol	71074-89-0	0.1 - 1

* Exact percentages may vary or are trade secret. Concentration range is provided to assist users in providing appropriate protections.

4. FIRST AID MEASURES

Inhalation:	Move to fresh air. If not breathing, give artificial respiration. If breathing is difficult, give oxygen. Get medical attention.
Skin contact:	Immediately flush skin with plenty of water (using soap, if available). Remove contaminated clothing and footwear. Get medical attention. Wash clothing before reuse. Thoroughly clean shoes before reuse.
Eye contact:	Immediately flush eyes with plenty of water for at least 15 minutes. Get medical attention.
Ingestion:	DO NOT induce vomiting unless directed to do so by medical personnel. Never give anything by mouth to an unconscious person. Get medical attention.
Symptoms:	See Section 11.
Notes to physician:	Treat symptomatically and supportively.

5. FIRE FIGHTING MEASURES

Extinguishing media:	Water spray (fog), foam, dry chemical or carbon dioxide.
Special firefighting procedures:	Wear self-contained breathing apparatus and full protective clothing, such as turn-out gear.
Unusual fire or explosion hazards:	In case of fire, keep containers cool with water spray. Closed containers may rupture (due to build up of pressure) when exposed to extreme heat.
Hazardous combustion products:	Oxides of carbon. Oxides of nitrogen. Irritating organic fragments.

6. ACCIDENTAL RELEASE MEASURES

Use personal protection recommended in Section 8, isolate the hazard area and deny entry to unnecessary and unprotected personnel.

Environmental precautions:	Do not allow product to enter sewer or waterways.
-----------------------------------	---

Clean-up methods:

Ensure adequate ventilation. Wear appropriate personal protective equipment. Refer to Section 8 "Exposure Controls / Personal Protection" prior to clean up. Soak up with inert absorbent material (e.g. sand, silica gel, acid binder, universal binder, sawdust). Scrape up spilled material and place in a closed container for disposal.

7. HANDLING AND STORAGE

Handling:

Use only with adequate ventilation. Prevent contact with eyes, skin and clothing. Do not breathe vapor and mist. Wash thoroughly after handling. Keep container closed.

Storage:

Keep container tightly closed and in a cool, well-ventilated place away from incompatible materials. Keep away from heat, spark and flame. Store in original container until ready to use.

8. EXPOSURE CONTROLS / PERSONAL PROTECTION

Employers should complete an assessment of all workplaces to determine the need for, and selection of, proper exposure controls and protective equipment for each task performed.

Hazardous Component(s)	ACGIH TLV	OSHA PEL	AIHA WEEL	OTHER
Poly[oxy(methyl-1,2-ethanediyl)], a-hydroxy-, ether with 2,2-bis(hydroxymethyl)-1,3-propanediol (4:1), 2-hydroxy-3-mercaptan	None	None	None	None
m-Phenylenebis(methylamine)	0.1 mg/m3 Ceiling (SKIN)	None	None	None
2,4,6-Tris(dimethylaminomethyl)phenol	None	None	None	None
Phenol	5 ppm TWA (SKIN)	5 ppm (19 mg/m3) PEL (SKIN)	None	None
3-(Trimethoxysilyl)propylamine	None	None	None	None
Bis[(dimethylamino)methyl]phenol	None	None	None	None

Engineering controls:

Provide adequate local exhaust ventilation to maintain worker exposure below exposure limits.

Respiratory protection:

Use a NIOSH approved air-purifying respirator if the potential to exceed established exposure limits exists.

Eyeface protection:

Safety goggles or safety glasses with side shields. Full face protection should be used if the potential for splashing or spraying of product exists. Safety showers and eye wash stations should be available.

Skin protection:

Use chemical resistant, impermeable clothing including gloves and either an apron or body suit to prevent skin contact.

9. PHYSICAL AND CHEMICAL PROPERTIES

Physical state:

Liquid

Color:

Amber, Translucent

Odor:

Amine, Mercaptan

Odor threshold:

Not available.

pH:

Not available.

Vapor pressure:

Not available.

Boiling point/range:

Not available.

Melting point/ range:

Not available.

Specific gravity:

1.04

Vapor density:

Not available.

Flash point:

> 93 °C (> 199.4 °F) Tagliabue closed cup

Flammable/Explosive limits - lower:

Not available.

Flammable/Explosive limits - upper:

Not available.

Autoignition temperature:	Not available.
Flammability:	Not applicable
Evaporation rate:	Not available.
Solubility in water:	Insoluble
Partition coefficient (n-octanol/water):	Not available.
VOC content:	3.77 %; 0.38 g/l EPA Method 24
Viscosity:	Not available.
Decomposition temperature:	Not available.

10. STABILITY AND REACTIVITY

Stability:	Stable under normal conditions of storage and use.
Hazardous reactions:	None under normal processing.
Hazardous decomposition products:	Oxides of carbon. Oxides of nitrogen. Ammonia. Irritating vapors.
Incompatible materials:	Strong acids and strong bases. Strong oxidizing agents. Sodium hypochlorite. Peroxides.
Reactivity:	Not available.
Conditions to avoid:	Elevated temperatures. Heat, flames, sparks and other sources of ignition. Store away from incompatible materials.

11. TOXICOLOGICAL INFORMATION

Relevant routes of exposure:	Skin, Inhalation, Eyes, Ingestion
-------------------------------------	-----------------------------------

Potential Health Effects/Symptoms

Inhalation:	Mists, vapors or liquid may cause severe irritation or burns. Dizziness.
Skin contact:	Causes skin burns. May cause allergic skin reaction.
Eye contact:	Causes serious eye damage. Corneal edema may give appearance of "blue haze" or "fog" around lights.
Ingestion:	If ingested, severe burns of the mouth and throat may occur, as well as perforation of the esophagus and the stomach.

Hazardous Component(s)	LD50s and LC50s	Immediate and Delayed Health Effects
Poly[oxy(methyl-1,2-ethanediyl)], a-hydro-w-hydroxy-, ether with 2,2-bis(hydroxymethyl)-1,3-propanediol (4:1), 2-hydroxy-3-mercaptan	None	No Records
m-Phenylenebis(methylamine)	None	Irritant, Liver, Kidney, Corrosive
2,4,6-Tris(dimethylaminomethyl)phenol	None	Irritant, Allergen
Phenol	Oral LD50 (Mouse) = 270 mg/kg Oral LD50 (Rat) = 317 mg/kg Oral LD50 (Rat) = 530 mg/kg Dermal LD50 (Rat) = 669 mg/kg Dermal LD50 (Rabbit) = 850 mg/kg	Blood, Cardiac, Corrosive, Developmental, Eyes, Irritant, Kidney, Liver, Mutagen, Nervous System, Skin, Vascular
3-(Trimethoxysilyl)propylamine	None	Irritant, Allergen
Bis[(dimethylamino)methyl]phenol	None	No Records

Hazardous Component(s)	NTP Carcinogen	IARC Carcinogen	OSHA Carcinogen (Specifically Regulated)
Poly[oxy(methyl-1,2-ethanediyl)], a-hydro-w-hydroxy-, ether with 2,2-bis(hydroxymethyl)-1,3-propanediol (4:1), 2-hydroxy-3-mercaptan	No	No	No
m-Phenylenebis(methylamine)	No	No	No
2,4,6-Tris(dimethylaminomethyl)phenol	No	No	No
Phenol	No	No	No
3-(Trimethoxysilyl)propylamine	No	No	No
Bis[(dimethylamino)methyl]phenol	No	No	No

12. ECOLOGICAL INFORMATION

Ecological information: Not available.

13. DISPOSAL CONSIDERATIONS

Information provided is for unused product only.

Recommended method of disposal:	Follow all local, state, federal and provincial regulations for disposal.
Hazardous waste number:	It is the responsibility of the user to determine if an item is hazardous as defined in the Resource Conservation and Recovery Act (RCRA) at the time of disposal. Product uses, transformations, mixtures, processes, etc., may render the resulting material hazardous, under the criteria of Ignitability, corrosivity, reactivity and toxicity characteristics of the Toxicity Characteristics Leaching Procedure (TCLP) 40 CFR 261.20-24.

14. TRANSPORT INFORMATION

The transport information provided in this section only applies to the material/formulation itself, and is not specific to any package/configuration.

U.S. Department of Transportation Ground (49 CFR)

Proper shipping name:	Amines, liquid, corrosive, n.o.s. (m-Xylylenediamine)
Hazard class or division:	8
Identification number:	UN 2735
Packing group:	II
DOT Hazardous Substance(s):	Phenol

International Air Transportation (ICAO/IATA)

Proper shipping name:	Amines, liquid, corrosive, n.o.s. (m-Xylylenediamine)
Hazard class or division:	8
Identification number:	UN 2735
Packing group:	II

Water Transportation (IMO/IMDG)

Proper shipping name:	AMINES, LIQUID, CORROSIVE, N.O.S. (m-Xylylenediamine)
Hazard class or division:	8
Identification number:	UN 2735
Packing group:	II

15. REGULATORY INFORMATION

United States Regulatory Information

TSCA 8 (b) Inventory Status:	All components are listed or are exempt from listing on the Toxic Substances Control Act Inventory.
TSCA 12 (b) Export Notification:	None above reporting de minimis
CERCLA/SARA Section 302 EHS:	Phenol (CAS# 108-95-2).
CERCLA/SARA Section 311/312:	Immediate Health, Delayed Health
CERCLA/SARA Section 313:	This product contains the following toxic chemicals subject to the reporting requirements of section 313 of the Emergency Planning and Community Right-To-Know Act of 1986 (40 CFR 372). Phenol (CAS# 108-95-2).
CERCLA Reportable quantity:	Phenol (CAS# 108-95-2) 1,000 lbs. (454 kg)
California Proposition 65:	This product contains a chemical known to the State of California to cause birth defects or other reproductive harm.

Canada Regulatory Information

CEPA DSL/NDL Status:	All components are listed on or are exempt from listing on the Canadian Domestic Substances List.
-----------------------------	---

16. OTHER INFORMATION

This safety data sheet contains changes from the previous version in sections: New Safety Data Sheet format.

Prepared by: Product Safety and Regulatory Affairs

Issue date: 10/05/2018

DISCLAIMER: The data contained herein are furnished for information only and are believed to be reliable. However, Henkel Corporation and its affiliates ("Henkel") does not assume responsibility for any results obtained by persons over whose methods Henkel has no control. It is the user's responsibility to determine the suitability of Henkel's products or any production methods mentioned herein for a particular purpose, and to adopt such precautions as may be advisable for the protection of property and persons against any hazards that may be involved in the handling and use of any Henkel's products. In light of the foregoing, Henkel specifically disclaims all warranties, express or implied, including warranties of merchantability and fitness for a particular purpose, arising from sale or use of Henkel's products. Henkel further disclaims any liability for consequential or incidental damages of any kind, including lost profits.



Revision Number: 004.0

Issue date: 08/11/2014

1. PRODUCT AND COMPANY IDENTIFICATION

Product name:	LOCTITE FM POXY PAK 1FO PT A	IDH number:	1324013
Product type:	Epoxy resin	Item number:	1324007_100805
Restriction of Use:	None identified	Region:	United States
Company address:	Contact information:		
Henkel Corporation	Telephone: (860) 571-5100		
One Henkel Way	MEDICAL EMERGENCY Phone: Poison Control Center		
Rocky Hill, Connecticut 06067	1-877-671-4608 (toll free) or 1-303-592-1711		
	TRANSPORT EMERGENCY Phone: CHEMTREC		
	1-800-424-9300 (toll free) or 1-703-527-3887		
	Internet: www.henkelna.com		

2. HAZARDS IDENTIFICATION

EMERGENCY OVERVIEW

WARNING: CAUSES SKIN IRRITATION.
MAY CAUSE AN ALLERGIC SKIN REACTION.
CAUSES SERIOUS EYE IRRITATION.

HAZARD CLASS	HAZARD CATEGORY
SKIN IRRITATION	2
EYE IRRITATION	2A
SKIN SENSITIZATION	1

PICTOGRAM(S)



Precautionary Statements

Prevention:	Avoid breathing vapors, mist, or spray. Wash thoroughly after handling. Contaminated work clothing should not be allowed out of the workplace. Wear eye and face protection. Wear protective gloves.
Response:	IF ON SKIN: Wash with plenty of soap and water. IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to remove. Continue rinsing. If skin irritation or rash occurs: Get medical attention. If eye irritation persists: Get medical attention. Take off contaminated clothing.
Storage:	Not prescribed
Disposal:	Dispose of contents and/or container according to Federal, State/Provincial and local governmental regulations.

Classification complies with OSHA Hazard Communication Standard (29 CFR 1910.1200) and is consistent with the provisions of the United Nations Globally Harmonized System of Classification and Labeling of Chemicals (GHS).

See Section 11 for additional toxicological information.

3. COMPOSITION / INFORMATION ON INGREDIENTS

Hazardous Component(s)	CAS Number	Percentage*
------------------------	------------	-------------

* Exact percentage is a trade secret. Concentration range is provided to assist users in providing appropriate protections.

4. FIRST AID MEASURES

Inhalation:	Move to fresh air. If not breathing, give artificial respiration. If breathing is difficult, give oxygen. Get medical attention.
Skin contact:	Immediately flush skin with plenty of water (using soap, if available). Remove contaminated clothing and footwear. Get medical attention. Wash clothing before reuse. Thoroughly clean shoes before reuse.
Eye contact:	Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes. Get medical attention.
Ingestion:	DO NOT induce vomiting unless directed to do so by medical personnel. Never give anything by mouth to an unconscious person. Get medical attention.
Symptoms:	See Section 11.

5. FIRE FIGHTING MEASURES

Extinguishing media:	Water spray (fog), foam, dry chemical or carbon dioxide.
Special firefighting procedures:	Wear self-contained breathing apparatus and full protective clothing, such as turn-out gear. In case of fire, keep containers cool with water spray.
Unusual fire or explosion hazards:	Closed containers may rupture (due to build up of pressure) when exposed to extreme heat.
Hazardous combustion products:	Oxides of carbon. Irritating vapors.

6. ACCIDENTAL RELEASE MEASURES

Use personal protection recommended in Section 8, isolate the hazard area and deny entry to unnecessary and unprotected personnel.

Environmental precautions:	Do not allow product to enter sewer or waterways.
Clean-up methods:	Remove all sources of ignition. Evacuate and ventilate spill area; dike spill to prevent entry into water system; wear full protective equipment during clean-up. Soak up with inert absorbent material (e.g. sand, silica gel, acid binder, universal binder, sawdust). Scrape up as much material as possible. Store in a partly filled, closed container until disposal. Refer to Section 8 "Exposure Controls / Personal Protection" prior to clean up.

7. HANDLING AND STORAGE

Handling:	Use only with adequate ventilation. Prevent contact with eyes, skin and clothing. Do not breathe vapor and mist. Wash thoroughly after handling. Keep container closed. Refer to Section 8.
Storage:	Keep container tightly closed and in a cool, well-ventilated place away from incompatible materials. Store away from heat, sparks, flames, or other sources of ignition.

For information on product shelf life contact Henkel Customer Service at (800) 243-4874.

8. EXPOSURE CONTROLS / PERSONAL PROTECTION

Employers should complete an assessment of all workplaces to determine the need for, and selection of, proper exposure controls and protective equipment for each task performed.

Hazardous Component(s)	ACGIH TLV	OSHA PEL	AIHA WEEL	OTHER
Epoxy resin	None	None	None	None

Engineering controls:	Provide adequate local exhaust ventilation to maintain worker exposure below exposure limits.
Respiratory protection:	Use a NIOSH approved air-purifying respirator if the potential to exceed established exposure limits exists.
Eye/face protection:	Safety goggles or safety glasses with side shields. Full face protection should be used if the potential for splashing or spraying of product exists. Safety showers and eye wash stations should be available.
Skin protection:	Use chemical resistant, impermeable clothing including gloves and either an apron or body suit to prevent skin contact.

9. PHYSICAL AND CHEMICAL PROPERTIES

Physical state:	Viscous, Liquid
Color:	Clear
Odor:	Mild
Odor threshold:	Not available.
pH:	Not available.
Vapor pressure:	0.03 mm hg (25 °C (77°F))
Boiling point/range:	> 260 °C (> 500°F)
Melting point/ range:	Not available.
Vapor density:	1.17
Flash point:	249 °C (480.2 °F) Pensky Martens closed cup
Flammable/Explosive limits - lower:	Not available.
Flammable/Explosive limits - upper:	Not available.
Autoignition temperature:	Not available.
Evaporation rate:	Not available.
Solubility in water:	Negligible
Partition coefficient (n-octanol/water):	Not available.
VOC content:	Not available.
Viscosity:	Not available.
Decomposition temperature:	Not available.

10. STABILITY AND REACTIVITY

Stability:	Stable under normal conditions of storage and use.
Hazardous reactions:	None under normal processing.
Hazardous decomposition products:	Oxides of carbon. Irritating vapors.
Incompatible materials:	Oxidizing agents. Acids. Bases.
Reactivity:	Not available.
Conditions to avoid:	Elevated temperatures. Heat, flames, sparks and other sources of ignition. Store away from incompatible materials.

11. TOXICOLOGICAL INFORMATION

Relevant routes of exposure:	Skin, Inhalation, Eyes, Ingestion
-------------------------------------	-----------------------------------

Potential Health Effects/Symptoms

Inhalation: Inhalation of vapors or mists of the product may be irritating to the respiratory system.
Skin contact: Causes skin irritation. May cause allergic skin reaction.
Eye contact: Causes serious eye irritation.
Ingestion: May cause gastrointestinal tract irritation if swallowed.

Hazardous Component(s)	LD50s and LC50s	Immediate and Delayed Health Effects
Epoxy resin	None	Allergen, Irritant

Hazardous Component(s)	NTP Carcinogen	IARC Carcinogen	OSHA Carcinogen (Specifically Regulated)
Epoxy resin	No	No	No

12. ECOLOGICAL INFORMATION

Ecological information: Not available.

13. DISPOSAL CONSIDERATIONS

Information provided is for unused product only.

Recommended method of disposal: Follow all local, state, federal and provincial regulations for disposal.

Hazardous waste number: Not a RCRA hazardous waste.

14. TRANSPORT INFORMATION

The transport information provided in this section only applies to the material/formulation itself, and is not specific to any package/configuration.

U.S. Department of Transportation Ground (49 CFR)

Proper shipping name: Not regulated
Hazard class or division: None
Identification number: None
Packing group: None

International Air Transportation (ICAO/IATA)

Proper shipping name: Environmentally hazardous substance, liquid, n.o.s. (Bisphenol-A Epichlorhydrin resin)
Hazard class or division: 9
Identification number: UN 3082
Packing group: III

Water Transportation (IMO/IMDG)

Proper shipping name: ENVIRONMENTALLY HAZARDOUS SUBSTANCE, LIQUID, N.O.S. (Bisphenol-A Epichlorhydrin resin)
Hazard class or division: 9
Identification number: UN 3082
Packing group: III
Marine pollutant: Bisphenol-A Epichlorhydrin resin

15. REGULATORY INFORMATION

United States Regulatory Information

TSCA 8 (b) Inventory Status: All components are listed or are exempt from listing on the Toxic Substances Control Act Inventory.
TSCA 12 (b) Export Notification: None above reporting de minimis
CERCLA/SARA Section 302 EHS: None above reporting de minimis
CERCLA/SARA Section 311/312: Immediate Health

CERCLA/SARA Section 313: None above reporting de minimis

California Proposition 65: This product contains a chemical known in the State of California to cause cancer. This product contains a chemical known to the State of California to cause birth defects or other reproductive harm.

Canada Regulatory Information

CEPA DSL/NDL Status: All components are listed on or are exempt from listing on the Canadian Domestic Substances List.

16. OTHER INFORMATION

This safety data sheet contains changes from the previous version in sections: New Safety Data Sheet format.

Prepared by: Sheila Gines, Regulatory Affairs Specialist

Issue date: 08/11/2014

DISCLAIMER: The data contained herein are furnished for information only and are believed to be reliable. However, Henkel Corporation and its affiliates ("Henkel") does not assume responsibility for any results obtained by persons over whose methods Henkel has no control. It is the user's responsibility to determine the suitability of Henkel's products or any production methods mentioned herein for a particular purpose, and to adopt such precautions as may be advisable for the protection of property and persons against any hazards that may be involved in the handling and use of any Henkel's products. In light of the foregoing, Henkel specifically disclaims all warranties, express or implied, including warranties of merchantability and fitness for a particular purpose, arising from sale or use of Henkel's products. Henkel further disclaims any liability for consequential or incidental damages of any kind, including lost profits.